


Equipment

Coll-O-Crimp Pumps

 Refer to safety information regarding Coll-O-Crimp hose, hose fittings and assembly equipment compatibility on pages 3-4.

T-481-110 • 110v Pump



For use with T-480-1.

Pump Specifications:

Dimensions: 14-14" High x 9-5/8" long x 9-5/8" wide
Weight: 32 lbs.

Operation Pressure:

0-10,000 PSI

Hydraulic Oil: Use Enerpac Oil ONLY

T-482-2 • Air/Hydraulic Pump



For use with T-480-1.

Pump Specifications:


Dimensions: 5-1/2" High, 14-5/8" long, 5-5/8" wide

Weight: 12 lbs.

Operation Pressure: 0-10,000 PSI

Hydraulic Oil: Use Enerpac Oil ONLY

T-421-FP • 4 Prong Female Electrical Outlet



All Boston 220v Coll-O-Crimp power pumps are equipped with a four prong electrical outlet as illustrated. To obtain corresponding female wall receptacle order T-421-FP. For use with T-421U, T-441 & T-433 pumps.

Repair and Replacement Items for Discontinued T-401-1 Pump

CATALOG NUMBER	DESCRIPTION
T-401-1B	Replacement Gasket between motor and square reservoir
T-401-1BC	Breather Cap for Fenner-Stone pumps
T-401-1G	Relief Handle Spring (Models prior to 1982)
T-401-1S	Toggle Switch
T-401-SVF	Shuttle Valve for Fenner-Stone pump

For repair and replacement items for the following pumps please contact an Enerpac Distributor at www.enerpac.com: T-402-2, T-403-2, T-460-2, T-462-2, T-480-2, T-480-3, T-481-110 & T-482-2.