



Engineered Better—Down to the Details.

It's true—the devil is in the details. That's why even our smallest parts are designed to make your job easier and more productive.

- DRX Impact Beds use our exclusive, anti-spin Square Washers to attach the impact bars to the Impact Bar Supports. These innovative washers work with standard, inexpensive carriage bolts. If ever needed, carriage bolts can be torched off and replaced for pennies. Other beds require expensive T bolts.
- On all DRX beds the four center Impact Bars Supports tilt 3° inward. It's a subtle detail that helps center the load on the belt.
- DRX beds are powder coated for better corrosion resistance, more durable finish and a more attractive appearance.
- The full range of Flexco's DRX Impact Beds meets and exceeds CEMA standards.

Fast, On-time Shipping.

Shipping times for our DRX3000 Dynamic Impact Beds are generally four weeks.

Contact Us Today.

As a partner in your productivity, Flexco can help you determine the best impact bed to meet your individual need. With the DRX3000 Dynamic Impact Bed there are no data sheets to fill out. Just call your Flexco Field Engineer and give the lump size, drop height and roller size with the corresponding CEMA rating, and he will recommend the ideal bed for your specific application.